



ZB3100 | Profibus connector DSUB, with switchable termination resistor, IP 20, for field installation

D-sub, plug, angled, male, 9-pin

Electrical data	
Mechanical data	
Installation size	D-sub
Connector type	plug
Configuration	angled
Contact type	male
Number of positions (face)	9-pin
Body colour	black
Body material	thermoplast
Max. cable outer diameter	8.5 mm
Environmental data	
Ambient temperature (operation)	0...+55 °C, 32...+131 °F
Protection class	IP 20

Dimensions	
A1	48.0 mm
A2	50.0 mm
A3	19.0 mm

Notes

- Illustrations similar

Ordering information	
ZB3100	9-pin D-sub connector for PROFIBUS (12 Mbaud) with switchable termination resistor

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlana® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.