


Z1101 | Plastic fiber optic, 980/1000 μm , PUR, \emptyset 5.5 mm, Kevlar strain relief, drag-chain suitable



Electrical data	
Transmission characteristics	damping: 650 nm (laser) < 190 dB/km; 660 nm (LED) < 260 dB/km
Mechanical data	
Cable structure	Plastic fiber optic 980/1000 μm made from PMMA with fluor polymeric cladding, diameter 1,0 mm
Conductor construction	PE buffer tube, nominal diameter 2.2 mm
Min. bending radius, moved	12.5 x outer cable diameter
Min. bending radius, fixed installation	9 x outer cable diameter
Weight	23 kg/km (15.41 lb/1000 ft)
Outer cable diameter	5.5 mm \pm 0.2 mm (0.216" \pm 0.0079")
Use	drag-chain suitable
Max. acceleration	4 m/s ²
Max. speed	4 m/s
Max. number of cycles	2 million
Jacket color	orange
Material jacket	PUR (polyurethane)
Wire color code	black
Printing on the jacket	- BECKHOFF Z1101 - I (meter imprint xxx,x m)
Printing color	black

Max. tensile load, dynamic	400 N
Max. tensile load, static	100 N
Environmental data	
Operation temperature range, moved	-20...+70 °C, -4...+158 °F
Ambient temperature, transport/storage	-40...+80 °C, -40...+176 °F
UV resistance	UV resistance of the outer jacket referred to DIN EN ISO 4892-2, Process A; UV application 500 hours
Oil resistance	Very good resistance to oil, gas, acids and bases
Special features	Plastic optical fiber for application in harsh industrial environments, for flexible applications as well as layout in cable conduits, pipes and cable racks, drag-chain suitable and direct connector assembly
Flame-retardant	flame-retardant
Halogen-free	according to IEC 60754-2
Approvals	Multimode fiber of the category A4a2 IEC 60793-2-40 and IEC 60794-2-42

Notes

- The following length tolerances apply: 2-3 %
- Illustrations similar

Ordering information	Length
Z1101	sold by the meter

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 05/2022

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.