



ZK2000-2122-6xxx | Sensor cable, PUR, 3 x 0.34 mm², torsion resistant

M8, plug, straight, male, 3-pin, A-coded – M8, socket, straight, female, 3-pin, A-coded

Plugs


Electrical data	Head A	Head B
Rated voltage	60 V (according to IEC 61076-2-104)	60 V (according to IEC 61076-2-104)
Rated current (signal/24V)	4 A at 40 °C (acc.to IEC 61076-2-104)	4 A at 40 °C (acc.to IEC 61076-2-104)
Shielding	no	no
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	M8	M8
Connector type	plug	socket
Configuration	straight	straight
Contact type	male	female
Number of positions (face)	3-pin	3-pin
Coding	A-coded	A-coded
Wire termination	crimp connection	crimp connection
Recommended torque, nut	0.4 Nm	0.4 Nm
Mating cycles	≥ 100 (according to IEC 60512-9a)	≥ 100 (according to IEC 60512-9a)
Way of locking	screw	screw
Weight per piece	0.028 kg (0.0617 lb)	0.028 kg (0.0617 lb)
Body colour	black	black
Body material	TPU, UL94	TPU, UL94
Coupling nut material	CuZn, Ni	CuZn, Ni
Seal	FPM	FPM
Contact carrier colour	red	red
Contact carrier material	TPU GF, UL 94	TPU GF, UL 94
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
Environmental data		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1
RoHS compliant	yes	yes

Ambient temperature (operation)	-30...+80 °C, -22...+176 °F	-30...+80 °C, -22...+176 °F
Protection class	IP 67 in screwed condition (according to IEC 60529)	IP 67 in screwed condition (according to IEC 60529)
Pollution level	3/2 (according to IEC 60664-1)	3/2 (according to IEC 60664-1)


Cable

Electrical data	
Rated voltage	300 V
Insulation resistance	≥ 500 MΩ/km
Wire resistance (signal/24V)	≤ 58.0 Ω/km (20 °C)
Test voltage	≥ 2000 V
Mechanical data	
Conductor construction (signal/24V)	42 x 0.10 mm, conductor category 6 according to DIN VDE 0295
Cross section	3 x 0.34 mm ² (AWG22)
Min. bending radius, moved	7.5 x outer cable diameter
Min. bending radius, fixed installation	4 x outer cable diameter
Weight	33.7 kg/km (22.65 lb/1000 ft)
Outer cable diameter	4.9 mm ± 0.2mm (0.193" ± 0.0079")
Conductor material (signal/24V)	copper bare
Shielding	no
Use	robotic- and drag chain suitable
Max. acceleration	5 m/s ²
Max. speed	3.3 m/s
Max. travel distance	100 m
Max. number of cycles	10 million
Jacket colour	black
Material jacket	PUR (polyurethane)
Material jacket, further characteristics of	weld-spatter resistant, low adhesion
Wire colour code	brown, blue, black
Wire insulation material	TPE (thermoplastic elastomer)
Printing on the jacket	XXXXm Beckhoff Automation GmbH & Co. KG -Germany-Sensor ZB9044-3x0,34mm ² E170315 cRUus AWM STYLE 20233 AWM I/II A/B 80°C 300V FT1
Printing colour	white
Torsion angle in °/m	max. ± 360°/m
Torsion speed	15 cycle/min.
Number of torsion cycles	10 million
Claimed torsion length	2 m
Environmental data	
Operation temperature range, moved	-30 °C... +105 °C, -22 °F...+221 °F, UL: up to +80 °C (+176 °F)
Operation temperature range, fixed installation	-40...+105 °C, -40...+221 °F
Oil resistance	very good oil and chemical resistance
LABS-free	yes
Flame-retardant	according to IEC 60332-1
Halogen-free	yes
Silicone-free	yes

Contact assembly



Dimensions



A1	39.60 mm
B1	33.60 mm

Notes

- Depending on the cable length (L), the following length tolerances apply:
 0 m...<0.2 m: ± 10 mm | 0.2...4.0 m: $+ 40$ mm | ≥ 4.0 m: $+ 1$ %
- Illustrations similar
- Further cable length on request. The last three digits of the ordering information is the cable length in decimeters, e.g. ZKxxxx-xxxx-x020 = cable length 2.00 m

Ordering information	Length
ZK2000-2122-6020	2.00 m
ZK2000-2122-6030	3.00 m
ZK2000-2122-6050	5.00 m
ZK2000-2122-6100	10.00 m
ZK2000-2122-6150	15.00 m

Accessories	
ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 02/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.