


# ZK2002-2324-0xxx | Sensor cable, PUR, 3 x 0.25 mm<sup>2</sup>, drag-chain suitable



M8, plug, angled, male, 3-pin, A-coded – M8, socket, angled, female, 3-pin, A-coded



## Plugs



Electrical data	Head A	Head B
Rated voltage	60 V (according to IEC 61076-2-104)	60 V (according to IEC 61076-2-104)
Rated current	-	3 A at 40 °C (according to IEC 61076-2-104)
Rated current (signal/24V)	4 A at 40 °C (acc.to IEC 61076-2-104)	4 A at 40 °C (acc.to IEC 61076-2-104)
Shielding	no	no
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	≥ 10 GΩ (according to IEC 60512-2)
Mechanical data		
Installation size	M8	M8
Connector type	plug	socket
Configuration	angled	angled
Contact type	male	female
Number of positions (face)	3-pin	3-pin
Coding	A-coded	A-coded
LED	-	with LED

Wire termination	-	crimp connection
Recommended torque, nut	0.4 Nm	0.4 Nm
Mating cycles	≥ 100 (according to IEC 60512-9a)	≥ 100 (according to IEC 60512-9a)
Way of locking	screw	screw
Weight per piece	0.028 kg (0.0617 lb)	0.028 kg (0.0617 lb)
Body color	black	transparent
Body material	TPU, UL94	TPU, UL94
Coupling nut material	CuZn, Ni	CuZn, Ni
Seal	FPM	FPM
Contact carrier color	red	red
Contact carrier material	TPU GF, UL 94	TPU GF, UL 94
Contact plating	Ni, Au gal.	Ni, Au gal.
Contact material	CuZn	CuZn
<b>Environmental data</b>		
Special features	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1	halogen-free, flame-resistant as per IEC 60332-1-2, oil-resistant as per DIN EN 60811-2-1
RoHS compliant	yes	yes
Ambient temperature (operation)	-30...+80 °C, -22...+176 °F	-30...+80 °C, -22...+176 °F
Protection rating	IP67 in screwed condition (according to IEC 60529)	IP67 in screwed condition (according to IEC 60529)
Pollution level	3/2 (according to IEC 60664-1)	3/2 (according to IEC 60664-1)

## Cable

<b>Electrical data</b>		
Rated voltage	≤ 300 V	
Insulation resistance	≥ 10 GΩ (according to IEC 60512-2)	
Wire resistance (signal/24V)	≤ 58.0 Ω/km (20 °C)	
Test voltage	≥ 3000 V	
<b>Mechanical data</b>		
Conductor construction (signal/24V)	32 x 0.10 mm	
Cross-section	3 x 0.25 mm <sup>2</sup> (AWG24)	
Min. bending radius, moved	6 x outer cable diameter	
Weight	28 kg/km (18.8 lb/1000 ft)	
Outer cable diameter	4.4 mm ± 0.15 mm (0.173" ± 0.0059")	
Shielding	no	
Use	drag-chain suitable	

Max. acceleration	10 m/s <sup>2</sup>
Max. speed	5 m/s
Max. number of cycles	10 million at max. 20 m travel distance, 2 million at max. 100 m travel distance
Jacket color	black
Material jacket	PUR (polyurethane)
Wire color code	brown, blue, black
Wire insulation material	PP (polypropylene)
Printing on the jacket	Li9Y11Y 3x0.25mm <sup>2</sup> E257058 CRUus (UL-Logo) AWM Style 20549 AWM II A/B 80°C 300 V FT2
Printing color	white
<b>Environmental data</b>	
Operation temperature range, moved	-25...+80 °C, -13...+176 °F
Oil resistance	Oil and greases resistant
Flame-retardant	according to cULus 20549
Halogen-free	DIN VDE 0472 part 815
CE	yes
UL	yes, UL E-file number: E257058

**Contact assembly****Dimensions**

A1	27.50 mm
A2	26.30 mm
B1	27.50 mm
B2	20.30 mm

## Notes

- Depending on the cable length (L), the following length tolerances apply:  
0 m...<0.2 m:  $\pm 10$  mm | 0.2...4.0 m: + 40 mm |  $\geq 4.0$  m: + 1 %
- Illustrations similar
- Further cable length on request.

Ordering information	Length
ZK2002-2324-0001	0.15 m

Accessories	
ZB8801-0000	torque wrench for hexagonal plugs, adjustable
ZB8801-0001	torque cable key, M8/wrench size 9, for ZB8801-0000



Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 08/2022

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.