


ZS2000-4723 | M12 Y splitter, IP 67, fully routed

M12, Y splitter, straight, male+female, 5-pin, A-coded

| Electrical data | |
|---------------------------------|--|
| Rated voltage | 30 V (according to IEC 61076-2-101) |
| Rated current | 4 A at 40 °C (according to IEC 61076-2-101) |
| Insulation resistance | ≥ 10 GΩ (according to IEC 60512-2) |
| Mechanical data | |
| Installation size | M12 |
| Connector type | Y splitter |
| Configuration | straight |
| Contact type | male+female |
| Number of positions (face) | 5-pin |
| Coding | A-coded |
| Recommended torque, nut | 0.6 Nm |
| Mating cycles | ≥ 100 (according to IEC 60512-9a) |
| Body colour | black |
| Body material | TPU |
| Seal | FPM |
| Contact carrier material | TPU |
| Contact material | CuZn, Ni b/Au 0.2 gal. |
| Environmental data | |
| RoHS compliant | yes |
| Ambient temperature (operation) | -25...+85 °C, -13...+185 °F |
| Protection class | IP 65/67 in screwed condition (according to IEC 60529) |
| Pollution level | 3/2 (according to IEC 60664-1) |



Dimensions

Notes

- Illustrations similar

Ordering information

ZS2000-4723

Y splitter, 1 x M12 (plug) – 2 x M12 (socket), IP 67, straight, 5-pin, A-coded, unshielded

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 06/2021

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.