



Motor cable ZK4500-8027-zzzz

Plug connector	Contact	Function	Core identification	Contact	Plug connector
  Mating view	U	U	black / 1	U	 
	V	V	black / 2	V	
	W	W	black / 3	W	
	PE	PE	green/yellow	PE	
	N	n. c.		n.c.	
	+	Brake +	black / 5	Brake +	
	-	Brake -	black / 6	Brake -	
	1	n. c.		n. c.	
	2	n. c.		n. c.	
	H	OCT + / Temp. +	white	OCT + / Temp. +	
	L	OCT - / Temp. -	blue	OCT - / Temp. -	

Catalog data	
Catalog text	10 mm ² with M40-speedtec® plug , highly flexible, for drag-chain use
Servomotor	AM806x-xTxxx and AM807x
Servo Drive	AX5000 (40 A)
Catalog description	(4x10mm ² + (2x1.5mm ²)C + (2xAWG22))

Electrical properties at 20°C	
Max. operating voltage	1000 VAC (UL)
Direct current resistance	≤ 55.0 Ω/km (AWG22) / ≤ 13.3 Ω/km (1.5 mm ²) / ≤ 1.91 Ω/km (10 mm ²), DIN EN 50395
Insulation resistance	≥ 500 MΩ x km, DIN EN 50395
Operating capacity at 800 Hz	score / screen ≤ 150 pF/m (10 mm ²), EN 50289-1-5



Mechanical properties	
Outside diameter d	20.9 ± 0.5 mm
Min. bending radius	10 x d
Max. driven speed	240 m/min
Max. acceleration	30 m/s ² (at 5 m movement)
Max. allowable travelling distance	20 m horizontal / 5 m vertical
Max. torsion	± 30°/m
Max. bending cycles	5 Mio.
Operating temperature	-20°C to +60°C
Shield optical	>85 %

Properties cable	
Material outer sheath	TPU, flame retardant, halogen free
Color	Orange, like RAL 2003
Weight	0.76 kg/m
RoHS conformity	Yes
Silicon-free	Yes
Halogen-free	DIN VDE 0472 T815
Flame resistance	IEC 60332-1-2 / UL758 cable flame test
Oil resistance outer sheath	HD 22.10 Appendix A / DIN EN60811-2-1
UL Approbation	UL758 (AWM) Style 21223 (Outer sheath) and Style 10492 (Core)

Properties motor plug	
Housing	brass, zinc diecast; nickel-plated and chromated
Connecting Nut	Brass, zinc diecast; nickel-plated
Contacts	brass gold plated
Seals	FPM/HNBR (Viton)
Clamp Ring	brass nickel-plated
Protection Type	connected: IP65 (IEC 60529)
Mating Cycles	min. 500

Properties AX5000 plug	
Contact material	Cu-Leg
Contact surface	tin-plated
Insulator	PBT
Licence	CSA, UL 1059
RoHS conformity	yes

Motor cable extension ZK4501-8027-zzzz

Plug connector	Contact	Function	Core identification	Contact	Plug connector
 Mating view 	U	U	black / 1	U	 Mating view 
	V	V	black / 2	V	
	W	W	black / 3	W	
	PE	PE	green/yellow	PE	
	N	n. c.		n.c.	
	+	Brake +	black / 5	+	
	-	Brake -	black / 6	-	
	1	n. c.		n. c.	
	2	n. c.		n. c.	
	H	OCT + / Temp. +	white	H	
	L	OCT - / Temp. -	blue	L	

Catalog data	Motor cable extension for motor cable ZK4500-8027-zzzz
Catalog text	10 mm ² with M40-speedtec® plug , highly flexible, for drag-chain use
Servomotor	AM806x-xTxxx and AM807x
Servo Drive	AX5000 (40 A)
Catalog description	(4x10mm ² + (2x1.5mm ²)C + (2xAWG22))

Electrical properties at 20°C	
Max. operating voltage	1000 VAC (UL)
Direct current resistance	≤ 55.0 Ω/km (AWG22) / ≤ 13.3 Ω/km (1.5 mm ²) / ≤ 1.91 Ω/km (10 mm ²), DIN EN 50395
Insulation resistance	≥ 500 MΩ x km, DIN EN 50395
Operating capacity at 800 Hz	score / screen ≤ 150 pF/m (10 mm ²), EN 50289-1-5

Mechanical properties	
Outside diameter d	20.9 ± 0.5 mm
Min. bending radius	10 x d
Max. driven speed	240 m/min
Max. acceleration	30 m/s ² (at 5 m movement)
Max. allowable travelling distance	20 m horizontal / 5 m vertical
Max. torsion	± 30°/m
Max. bending cycles	5 Mio.
Operating temperature	-20°C to +60°C
Shield optical	>85 %

Properties cable	
Material outer sheath	TPU, flame retardant, halogen free
Color	Orange, like RAL 2003
Weight	0.76 kg/m
RoHS conformity	Yes
Silicon-free	Yes
Halogen-free	DIN VDE 0472 T815
Flame resistance	IEC 60332-1-2 / UL758 cable flame test
Oil resistance outer sheath	HD 22.10 Appendix A / DIN EN60811-2-1
UL Approbation	UL758 (AWM) Style 21223 (Outer sheath) and Style 10492 (Core)

Properties motor plug	
Housing	brass, zinc diecast; nickel-plated and chromated
Connecting Nut	Brass, zinc diecast; nickel-plated
Contacts	brass gold plated
Seals	FPM/HNBR (Viton)
Clamp Ring	brass nickel-plated
Protection Type	connected: IP65 (IEC 60529)
Mating Cycles	min. 500