





Motor cable extension ZK4501-8025-zzzz

Plug connector	Contact	Function	Core identification	Contact	Plug connector
 <p>Mating view</p> 	U	U	black / 1	U	 <p>Mating view</p> 
	V	V	black / 2	V	
	W	W	black / 3	W	
	PE	PE	green/ yellow	PE	
	N	n. c.		n.c.	
	+	Brake +	black / 5	+	
	-	Brake -	black / 6	-	
	1	n. c.		n. c.	
	2	n. c.		n. c.	
	H	OCT + / Temp. +	white	H	
	L	OCT - / Temp. -	blue	L	

Catalog data	Motor cable extension for motor cable ZK4500-8025-zzzz
Catalog text	4 mm ² with M40-speedtec® plug,, highly flexible, for drag-chain use
Servomotor	AM807x
Servo Drive	AX5000 (18...25 A)
Catalog description	(4x4mm ² + (2x1.0mm ²)C + (2xAWG22))

Electrical properties at 20°C	
Max. operating voltage	1000 VAC (UL)
Direct current resistance	≤ 55.0 Ω/km (AWG22) / ≤ 20.0 Ω/km (1.0 mm ²) / ≤ 4.95 Ω/km (4 mm ²), DIN EN 50395
Insulation resistance	≥ 500 MΩ x km, DIN EN 50395
Operating capacity at 800 Hz	score / screen ≤ 150 pF/m (4 mm ²), EN 50289-1-5

Mechanical properties	
Outside diameter d	15.9 ± 0.4 mm
Min. bending radius	5 x d for fixed installation / 7 x d for dynamic use
Max. driven speed	240 m/min
Max. acceleration	30 m/s ² (at 5 m movement)
Max. allowable travelling distance	20 m horizontal / 5 m vertical
Max. torsion	± 30°/m
Max. bending cycles	5 Mio.
Operating temperature	-20°C to +60°C
Shield optical	>85 %

Properties cable	
Material outer sheath	TPU, flame retardant, halogen free
Color	Orange, like RAL 2003
Weight	0.42 kg/m
RoHS conformity	Yes
Silicon-free	Yes
Halogen-free	DIN VDE 0472 T815
Flame resistance	IEC 60332-1-2 / UL758 cable flame test
Oil resistance outer sheath	HD 22.10 Appendix A / DIN EN60811-2-1
UL Approbation	UL758 (AWM) Style 21223 (Outer sheath) and Style 10492 (Core)

Properties motor plug	
Housing	brass, zinc diecast; nickel-plated and chromated
Connecting Nut	Brass, zinc diecast; nickel-plated
Contacts	brass gold plated
Seals	FPM/HNBR (Viton)
Clamp Ring	brass nickel-plated
Protection Type	connected: IP 65 (IEC 60529)
Mating Cycles	min. 500