

# C9900-K742...K744 | Power cable, PUR, 2 x 0.75 mm<sup>2</sup>, drag-chain suitable, black



M12, socket, straight, female, 5-pin, A-coded – open end



## Plugs


Electrical data	Head A	Head B
Rated voltage	250 V (according to IEC 61076-2-101)	-
Rated current	4 A at 40 °C (according to IEC 61076-2-101)	-
Shielding	no	-
Contact resistance	< 10 mΩ	-
Insulation resistance	≥ 100 GΩ (according to IEC 60512)	-
Mechanical data		
Installation size	M12	open end
Connector type	socket	-
Configuration	straight	-
Contact type	female	-
Number of positions (face)	5-pin	-
Coding	A-coded	-
Recommended torque, nut	0.6 Nm	-

Mating cycles	≥ 100 (according to IEC 60512-9a)	-
Way of locking	screw	-
Body color	black	-
Coupling nut material	GD-Zn, Ni	-
Seal	FPM	-
Contact carrier color	red	-
Contact carrier material	PA, UL 94	-
Contact material	CuZn, Ni b/Au 0.2 gal.	-
<b>Environmental data</b>		
RoHS compliant	yes	-
Protection rating	IP65/67 in screwed condition (according to IEC 60529)	-
Pollution level	3/2 (according to IEC 60664-1)	-


## Cable

<b>Electrical data</b>		
Rated voltage	300 V	
Wire resistance	≤ 26 Ω/km (20 °C)	
Test voltage	3000 V	
<b>Mechanical data</b>		
Cross-section	2 x 0.75 mm <sup>2</sup> (AWG18)	
Min. bending radius, moved	10 x outer cable diameter	
Conductor material	copper bare	
Shielding	no	
Use	drag-chain suitable	
Max. acceleration	10 m/s <sup>2</sup>	
Max. speed	5 m/s	
Jacket color	black	
Material jacket	PUR (polyurethane)	
Wire color code	brown, blue	
Wire insulation material	PP (polypropylene)	
Printing color	white	
<b>Environmental data</b>		
Flame-retardant	according to cULus 20549	
Halogen-free	DIN VDE 0472 part 815	
RoHS compliant	yes	

## Contact assembly



## Dimensions



## Notes

- Depending on the cable length (L), the following length tolerances apply:  
 < 10.0 m : ± 40 mm | 20.0 m : ± 70 mm
- Illustrations similar
- Further cable length on request.

## CE, UL

CE yes

## Ordering information

## Length

C9900-K742	5.00 m
C9900-K743	10.00 m
C9900-K744	20.00 m



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be

trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 01/2024

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.