






AX2090-TT80-0016

Isolating transformer 3-phase, 16 kVA, 19.2 A AC

For AX8620-0000, 3-phase supply, for ungrounded delta and corner-grounded delta

Electrical data	
Rated input voltage	3 x 480 V AC
Output voltage	3 x 480 V AC
Rated Power	16 000 VA
Rated output current	3 x 19.2 A
Short circuit voltage	4.4 %
Frequency	50 - 60 Hz
Vector group	Dyn5
Insulation group	ta. 40 °C Cl.F
Mechanical data	
Connection	Screw-type terminal 10 mm ²
Fixing method	Fixing rail
Mounting holes	Ø 14.5 x 24.0 mm
Protection class	IP 00
Weight	120 kg
Environmental data	
Max. Temperature	40 °C
Approvals	cRUus, UL 1561, CSA 22.2 (E327358)
Standards	VDE 0570 part 2-4, DIN EN 61558 part 1 with part 2-4

Dimensions



Notes

- Illustrations similar
- The last three digits of the ordering information is the rated power in kVA

Ordering information	Rated Power
AX2090-TT80-0016	16 kVA

Beckhoff®, TwinCAT®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 09/2020

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.