



ZS3000-0103 | Miniature thermocouple connector, green, Thermocouple: NiCr-Ni, type K according to DIN EN 60584, Variant: Quick Wire, packaging unit = 10 pieces



plug



Mechanical data	
Connector type	plug
Wire termination	Quick Wire
Body color	green
Body material	plastic
Max. wire cross-section	AWG24 ... AWG20 (0.22 mm ² ... 0.5 mm ²)
Environmental data	
Special features	Thermocouple: NiCr-Ni, type K according to DIN EN 60584
Ambient temperature (operation)	+220 °C, +428 °F

Dimensions	
A1	25.6 mm
A2	16.1 mm

Notes

- Illustrations similar

Ordering information

ZS3000-0101

thermocouple plug in miniature version, green, thermocouple: NiCr-Ni, type K according to DIN EN 60584, packaging unit = 10 pieces



Products marked with a crossed-out wheeled bin shall not be discarded with the normal waste stream. The device is considered as waste electrical and electronic equipment. The national regulations for the disposal of waste electrical and electronic equipment must be observed.

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 06/2023

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.