

## ZS4800-2001 | Mains input connector, DC link, 24 V DC power supply, ext. braking resistor, X01

grid 7.62mm, female, IP 20, 10-pin, clamping type

### Connector

Electrical data	
Rated voltage	1000V (according to IEC 60664-1 / IEC 61984) 600 V (UL)
Rated current	41 A at 40°C (according to IEC 60664-1 / IEC 61984) 40 A at 40°C (UL)
Rated impulse voltage	6000 V (according to IEC 60664-1 / IEC 61984)
Overvoltage category	III / II (according to IEC 60664-1 / IEC 61984)
Shield	no
Contact resistance	<5mΩ
Mechanical data	
Installation size	7.62 mm
Connector type	plug
Configuration	straight
Contact type	female
Number of positions	10
Wire termination	clamping type
Recommended torque, nut	0.5 – 0.6 Nm
Mating cycles	25
Weight	0.055 kg/pcs
Contact carrier color	black
Contact carrier material	PA GF, UL 94 V-0
Contact material	copper alloy
Contact plating	tinned
max. wire cross section	0.25 – 6 mm <sup>2</sup> (AWG24 – AWG10)
Environmental data	
Other characteristics	RoHS-conform, UL-certified, UL 94-V0
Operation temperature range in °C	-50°C up to 125°C
Protection level	IP20
Degree of pollution	3/2
Ordering information	
ZS4800-2001	Mains input connector, DC link, 24 V DC power supply, ext. braking resistor, X01, grid 7.62mm, female, IP 20, 10-pin, clamping type