



# ZK4810-0020-xxxx | Encoder cable, EnDat 2.2, shielded, M12 plug,



D-sub, socket, angled, male, 15-pin – M12, socket, straight, female, 8-pin, A-coded



## Plugs


Electrical data	Head A	Head B
Rated voltage	-	30 V (according to IEC 61076-2-101)
Rated current	-	2 A at 40 °C (according to IEC 61076-2-101)
Shielding	-	yes
Insulation resistance	-	≥ 100 MΩ (according to IEC 60512)
Mechanical data		
Accessories type	Connectors/Cables	Connectors/Cables
Installation size	D-sub	M12
Connector type	socket	socket
Configuration	angled	straight
Contact type	male	female
Number of positions (face)	15-pin	8-pin
Coding	-	A-coded
Wire termination	solder connection	screw connection


Recommended torque, nut	-	0.6 Nm
Mating cycles	-	≥ 100 (according to IEC 60512-9a)
Way of locking	screw	screw
Weight per piece	0.055 kg (0.1213 lb)	0.046 kg (0.1014 lb)
Body color	metal	metal
Body material	zinc diecast/nickel plated	GD-Zn, Ni
Coupling nut material	-	GD-Zn, Ni
Seal	-	elastomers
O-ring	-	NBR
Contact carrier color	-	black
Contact carrier material	-	PA, UL 94
Contact plating	-	Ni, Au gal.
Contact material	-	CuZn
Max. wire cross-section	-	AWG20 (0.5 mm <sup>2</sup> )
Max. cable outer diameter	-	4 - 8 mm
<b>Environmental data</b>		
RoHS compliant	-	yes
Ambient temperature (operation)	-40...+120 °C, -40...+248 °F	-30...+85 °C, -22...+185 °F
Protection rating	IP20	IP65/67 in screwed condition (according to IEC 60529)
Pollution level	-	3/2 (according to IEC 60664-1)

## Cable

<b>Electrical data</b>		
Operating voltage	30 V	
Insulation resistance	≥ 1 GΩ * km	
Wire resistance	0.20 mm <sup>2</sup> : ≤ 95.0 Ω/km, 0.38 mm <sup>2</sup> : ≤ 55.0 Ω/km	
Test voltage	500 V (wire/wire and wire/screen)	
<b>Mechanical data</b>		
Cross-section	2 x 2 x 0.20 mm <sup>2</sup> + 1 x 2 x 0.38 mm <sup>2</sup>	
Min. bending radius, moved in drag-chain	70 mm	
Min. bending radius, fixed installation	35 mm	
Weight	63 kg/km (42.330 lb/1000 ft)	
Outer cable diameter	6.95 ± 0.15 mm	
Conductor material	copper, tinned	
Optical covering factor of shielding	≥ 85%	

Use	drag-chain suitable
Max. acceleration	30 m/s <sup>2</sup>
Max. speed	5 m/s
Max. number of cycles	10 million
Jacket color	green
Material jacket	PUR (polyurethane)
Wire insulation material	PP (polypropylene)
Printing color	black
Torsion angle in °/m	max. ± 30 °/m
Max. tensile load, dynamic	20 N/mm <sup>2</sup>
<b>Environmental data</b>	
Operation temperature range, moved	-40...+80 °C, -40...+176 °F
Operation temperature range, fixed installation	-50...+80 °C, -58...+176 °F
Oil resistance	according to UL 1581
Flame-retardant	IEC 60332-1-2, UL/CSA FT1, UL VW1
CFC-free	yes
Halogen-free	yes
Silicone-free	yes
RoHS compliant	yes
Approvals	UL-Style 20236 80°C 30V

**Contact assembly****Dimensions**



A1	46.00 mm
A2	41.00 mm
B1	approx. 54 mm
B2	Ø 20.00 mm

## Notes

- Depending on the cable length (L), the following length tolerances apply:  $\pm 2\text{-}3\%$
- Illustrations similar
- The last three digits of the ordering information is the cable length in decimeters, e.g. ZK4xxx-xxxx-x020 = cable length 2.00 m

Ordering information	Length
ZK4810-0020-xxxx	xxxx = cable length in decimeters
xxxx = 0050	example for 5 m length
	sold by the meter, admissible total cable length see documentation of Servo Drive

Beckhoff®, TwinCAT®, TwinCAT/BSD®, TC/BSD®, EtherCAT®, EtherCAT G®, EtherCAT G10®, EtherCAT P®, Safety over EtherCAT®, TwinSAFE®, XFC®, XTS® and XPlanar® are registered trademarks of and licensed by Beckhoff Automation GmbH. Other designations used in this publication may be trademarks whose use by third parties for their own purposes could violate the rights of the owners.

© Beckhoff Automation GmbH & Co. KG 06/2022

The information provided in this brochure contains merely general descriptions or characteristics of performance which in case of actual application do not always apply as described or which may change as a result of further development of the products. An obligation to provide the respective characteristics shall only exist if expressly agreed in the terms of contract.